

shunt release 110-415 V AC, for miniature circuit breaker 5SL4, 5SY, 5SP, RCBO 5SU1, FI 5SV (for 5SU1 handle coupler 5ST3805-1 is required)



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Wyzwalacz prądu roboczego
wykonanie produktu	do zamontowania
trwałość elektryczna (w cyklach łączenia) / typowy	20 000
Napięcie zasilania	
napięcie robocze	
• wartość znamionowa	230 V
Stopień ochrony IP	IP20
Szczegóły produktu	
rozszerzenie produktu	Wyzwalacz wzrostowy
Liczba	
liczba styków alarmowych	0
liczba zestyków rozwiernych	0
liczba zestyków zwiernych	2
liczba zestyków przełącznych	0
Połączenia	

przekrój możliwego do podłączenia przewodu	0,5 ... 2,5 mm ²
moment dokręcenia / przy zacisku śrubowym	0,5 N·m
rodzaj przekrojów poprzecznych możliwych do podłączenia przewodów / przy przewodach AWG	24 ... 12

Konstrukcja mechaniczna

wysokość	90 mm
szerokość	18 mm
głębokość	70 mm
masa netto	100 g
<ul style="list-style-type: none"> • podczas pracy • podczas magazynowania 	-25 ... +55 °C -40 ... +75 °C

Certyfikaty

Declaration of Conformity	other	Railway
---------------------------	-------	---------



EG-Konf.

[Environmental Confirmations](#)

[Miscellaneous](#)

[Vibration and Shock](#)

Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5ST3030>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/5ST3030>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3030

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





