

shunt release 110-480 V AC for miniature circuit breaker according to UL 489



Wersja	
Nazwa markowa produktu	SETRON
oznaczenie produktu	Wyzwalacz prądu roboczego
wykonanie produktu	do zamontowania
trwałość elektryczna (w cyklach łączenia) / typowy	12 000
Napięcie zasilania	
napięcie robocze	
• wartość znamionowa	480 V
Stopień ochrony IP	IP20
Szczegóły produktu	
rozszerzenie produktu	Wyzwalacz wzrostowy
Liczba	
liczba styków alarmowych	0
liczba zestyków rozwiernych	0
liczba zestyków zwiernych	0
liczba zestyków przełącznych	0
Połączenia	

przekrój możliwego do podłączenia przewodu	0,5 ... 2,5 mm ²
moment dokręcenia / przy zacisku śrubowym	0,8 N·m
rodzaj przekrojów poprzecznych możliwych do podłączenia przewodów / przy przewodach AWG	24 ... 12

Konstrukcja mechaniczna

wysokość	110 mm
szerokość	18 mm
głębokość	70 mm
masa netto	117 g

Certyfikaty

General Product Approval

Declaration of Conformity



Więcej informacji

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=5ST3030-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pl/ps/5ST3030-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3030-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

