

Product fiche

Delegated Regulation (EU) 812/2013

Supplier name or trademark	SYGONIX
Model identifier	2886554
Declared load profile	3XS
Water heating energy efficiency class	B
Water heating energy efficiency	34 %
Annual electricity consumption	88 kWh
Annual fuel consumption	88 GJ
Other Information	
Thermostat temperature settings	30-50#
Sound power level (Indoors)	15 dB
Specific precautions	1. Erect product vertically, avoid tilting or upside-down installation. 2. Connect water source before power supply during first use and after water cut-off. 3. Do not use electricity when water in appliance is frozen. 4 . Do not install appliance outdoors or in freezing areas. 5. Maximum water temperature is 50# when in use . 6. Do not cover plug, socket, or appliance with towels or other items. Do not use wet hands to pull the plug . 7. Do not use with other high-power appliances when power capacity is low. 8. Outlet must only be connected to specified faucet or connector, no choke element. 9. Descale spray cap regularly. 10. Ground appliances. 11. Replace damaged power cord with professional personnel. 12. Permanently connect appliance to fixed wiring with fully disconnected device under voltage grade III. 13. Max. inlet pressure is 0.4 MPa, min. is 0.04 MPa. 14. Disconnect power when not in use for safety.