SIEMENS

Ficha técnica 3VL9563-7DC30

ETU VL630, 3-pole, line protection thermal-magnetic, LI IR=500...630A, overload protection II=3250...6500A, short-circuit protection screw terminal conn. in scope of delivery of



Figure similar

Versão	
Nome da marca do produto	SENTRON
Peso líquido	1,52 kg

Certificados

Reservado o direito a alterações
© Copyright Siemens

General Product Approval	EMC	Declaration of Conformity	Test Certificates	Shipping Approval	
Miscellaneous	C-Tick	EG-Konf.	Special Test Certificate	PRS	RINA

Shipping Approval	other			
RMRS	Environmental Confirmations	Confirmation	Miscellaneous	Manufacturer Declaration

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,…)
http://www.siemens.com/lowvoltage/catalogs

Industry Mall (Online ordering system)
https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3VL9563-7DC30

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)
https://support.industry.siemens.com/cs/ww/pt/ps/3VL9563-7DC30

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)
http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VL9563-7DC30

CAx-Online-Generator
http://www.siemens.com/cax

Tender specifications
http://www.siemens.com/specifications

Reservado o direito a alterações
© Copyright Siemens