

SR60 base DIAZED DII 3-pole 500 V AC DC for adaptor screw for 5/10 mm busbar thickness with clamp-type terminals



[Figure similar](#)

Versão	
Nome da marca do produto	SETRON
Designação do produto	Sistema de fusíveis DIAZED
Execução do produto	CASQUILHO SR60
Versão do casquilho para fusíveis	Fusível
Dados técnicos gerais	
Quantidade de pólos	3
Tamanho do sistema de fusíveis / segundo a DIN EN 60269-1	DII
Tensão de alimentação	
Corrente / com AC / valor estipulado	25 A
Tensão de alimentação / com AC / valor estipulado	500 V
Detalhes do produto	
Componente do produto / Cobertura	Não
Projeto mecânico	
Altura	200 mm

Largura	42 mm
Profundidade	43,5 mm
Peso líquido	226 g
material / da caixa	Outros

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2 F
- segundo a IEC 81346-2:2009 F

Test Certificates

[Type Test Certificates/Test Report](#)

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=5SF6015>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/5SF6015>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF6015

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

