

SENTRON, cylindrical fuse holder, 10x38 mm, 3-pole, In: 32 A, Un AC: 690 V, for busbar system 8US 60 mm



Versão	
Nome da marca do produto	SENTRON
Designação do produto	Suporte de encaixe de fusível cilíndrico
Execução do produto	para sistema de barramento 8US 60mm
Dados técnicos gerais	
Quantidade de pólos	3
Tamanho do cartucho de fusíveis	10x38 mm
Tensão de alimentação	
Corrente / com AC / valor estipulado	32 A
Tensão de serviço	
• com AC / valor estipulado	690 V
Classe de protecção IP	IP20
Projeto mecânico	
Altura	200 mm
Largura	27 mm
Profundidade	79 mm
Certificados	

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity



Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW7431>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW7431>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7431

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





