

SITOR cylindrical fuse link, 22x58 mm, 40 A, aR, Un AC: 690 V, Un DC: 700 V, DC according to UL



Versão	
Nome da marca do produto	SETRON
Designação do produto	SITOR Elemento de fusível cilíndrico
Execução do produto	CC de acordo com a UL
Dados técnicos gerais	
Classe de operação do elemento fusível	aR (ultra-rápido)
Tamanho do elemento fusível	22x58 mm
Tipo de tensão	CA
Corrente / com AC / valor estipulado	40 A
Tensão de alimentação / com DC	700 V
Tensão de serviço / valor estipulado	690 V
Dissipação	
Potência de perda [W] / com valor de corrente estipulado / com AC / com estado de funcionamento quente / por pólo	8,5 W
Circuito principal	
Corrente de funcionamento / valor nominal	40 A
Detalhes do produto	

Componente do produto / Detector de choque	Não
Posição de montagem	opcional, preferível vertical
Peso líquido	56 g

### Certificados

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F  
F

### General Product Approval

### Declaration of Conformity



CSA



UR

[Miscellaneous](#)



EG-Konf.

### Outras informações

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NC2240>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pt/ps/3NC2240>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NC2240](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2240)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



