

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,
Protection class 1, H: 1950 mm, W: 1050 mm, T: 250 mm, RAL 7035



Versão	
Nome da marca do produto	ALPHA 630
Designação do produto	Armário fixo
Execução do produto	com painel lateral aberto
Processamento da superfície	Revestido a pó

Classe de proteção	
Classe de protecção IP	IP55
Aptidão para acção conjunta / Protecção contra raios	Sim
Aptidão para utilização / para uso exterior	Não

Aparência	
Código da cor RAL	RAL 7035
Componente do produto	
• Entrada de cabos	Sim
• Placa de montagem	Não
Expansão do produto / opcional / Encadeamento	Sim

Projeto mecânico	
Altura	1 950 mm
Largura	1 050 mm

Profundidade	250 mm
Profundidade da montagem	250 mm
Peso líquido	64 kg
material / da caixa	Aço

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

U

UC

General Product Approval	Declaration of Conformity	Test Certificates
---------------------------------	----------------------------------	--------------------------



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

other

[Miscellaneous](#)

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=8GK1323-8KP43>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/8GK1323-8KP43>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KP43

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



