

ALPHA 630, Floor-mounted cabinet, IP55, Protection class 2, H:  
1950 mm, W: 800 mm, T: 250 mm, RAL 7035



Versão	
Nome da marca do produto	ALPHA 630
Designação do produto	Armário fixo
Processamento da superfície	Revestido a pó

  

Classe de protecção	
Classe de protecção IP	IP55
Aptidão para acção conjunta / Protecção contra raios	Sim
Aptidão para utilização / para uso exterior	Não

  

Aparência	
Código da cor RAL	RAL 7035
Componente do produto	
• Entrada de cabos	Sim
• Placa de montagem	Não
Expansão do produto / opcional / Encadeamento	Sim

  

Projeto mecânico	
Altura	1 950 mm
Largura	800 mm
Profundidade	250 mm

Profundidade da montagem	250 mm
Peso líquido	53,3 kg
material / da caixa	Aço

## Certificados

### Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

U  
UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

VDE

EG-Konf.

### other

[Miscellaneous](#)

## Outras informações

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=8GK1333-8KN33>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/8GK1333-8KN33>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1333-8KN33](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1333-8KN33)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



