

DIAZED base NDZ 25 A 500 V AC DC Top contact/top contact



Figure similar

Versão	
Nome da marca do produto	SETRON
Designação do produto	Sistema de fusíveis DIAZED
Execução do produto	DIAZED-casquilho, contacto de cabeça / contacto de cabeça
Versão do casquilho para fusíveis	Fusível
Dados técnicos gerais	
Quantidade de pólos	1
Tamanho do sistema de fusíveis / segundo a DIN EN 60269-1	NDz
Tensão de alimentação	
Corrente / com AC / valor estipulado	25 A
Tensão de alimentação / com AC / valor estipulado	500 V
Detalhes do produto	
Componente do produto / Cobertura	Não
Projeto mecânico	
Altura	49 mm

Largura	29 mm
Profundidade	44,6 mm
Peso líquido	65 g
material / da caixa	Porcelana

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2 F
- segundo a IEC 81346-2:2009 F

Declaration of Conformity



EG-Konf.

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=5SF1012>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/5SF1012>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF1012

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



