

SENTRON, cylindrical fuse holder, 10 x 38 mm, 2-pole, In: 30 A, Ue DC: 1000 V, for photovoltaic application



Versão	
Nome da marca do produto	SENTRON
Designação do produto	Suporte de encaixe de fusível cilíndrico
Execução do produto	para utilização fotovoltaica
Dados técnicos gerais	
Quantidade de pólos	2
Tamanho do cartucho de fusíveis	10x38 mm
Tensão de alimentação	
Corrente / com AC / valor estipulado	30 A
Tensão de serviço	
• com DC / valor estipulado	1 000 V
Classe de protecção IP	IP20
Projeto mecânico	
Altura	85 mm
Largura	36 mm
Profundidade	65 mm
Peso líquido	122 g

## Certificados

### Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

### General Product Approval

### Declaration of Conformity

other



CCC



CSA



UL



EG-Konf.

[Miscellaneous](#)

## Outras informações

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW7023-4>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW7023-4>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7023-4](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7023-4)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>

