

SENTRON, cylindrical fuse holder, 10x38 mm, 3P+N, In: 32 A, Un
AC: 690 V



Versão

Nome da marca do produto	SENTRON
Designação do produto	Suporte de encaixe de fusível cilíndrico

Dados técnicos gerais

Quantidade de pólos	4
Quantidade de pólos / anotação	3P+N
Tamanho do cartucho de fusíveis	10x38 mm

Tensão de alimentação

Corrente / com AC / valor estipulado	32 A
Tensão de serviço	
• com AC / valor estipulado	690 V
Classe de protecção IP	IP20

Projeto mecânico

Altura	81 mm
Largura	54 mm
Profundidade	64 mm
Peso líquido	196 g

Certificados

Indicadores de referência

- | | |
|------------------------------|---|
| • segundo a DIN EN 61346-2 | F |
| • segundo a IEC 81346-2:2009 | F |

General Product Approval

Declaration of Conformity



UR



EG-Konf.

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW7063>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW7063>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7063

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





