

SETRON, cylindrical fuse holder, 14x51 mm, 2-pole, In: 50 A, Un AC: 690 V



Versão	
Nome da marca do produto	SETRON
Designação do produto	Suporte de encaixe de fusível cilíndrico
Dados técnicos gerais	
Quantidade de pólos	2
Tamanho do cartucho de fusíveis	14x51 mm
Tensão de alimentação	
Corrente / com AC / valor estipulado	50 A
Tensão de serviço	
• com AC / valor estipulado	690 V
Classe de protecção IP	IP20
Projeto mecânico	
Altura	90 mm
Largura	54 mm
Profundidade	70 mm
Peso líquido	214 g
Certificados	

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

General Product Approval

Declaration of Conformity

Test Certificates



UR



EG-Konf.

[Miscellaneous](#)

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW7121>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW7121>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7121

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





