

SETRON, cylindrical fuse holder, 22x58 mm, 1-pole, In: 100 A, Un AC: 690 V



### Versão

Nome da marca do produto	SETRON
Designação do produto	Suporte de encaixe de fusível cilíndrico

### Dados técnicos gerais

Quantidade de pólos	1
Tamanho do cartucho de fusíveis	22x58 mm

### Tensão de alimentação

Corrente / com AC / valor estipulado	100 A
Tensão de serviço	
• com AC / valor estipulado	690 V
Classe de protecção IP	IP20

### Projeto mecânico

Altura	117 mm
Largura	36 mm
Profundidade	70 mm
Peso líquido	154 g

### Certificados

#### Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

#### Declaration of Conformity

#### Test Certificates



EG-Konf.

[Miscellaneous](#)

#### Outras informações

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW7211>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW7211>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7211](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7211)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>





