

ALPHA 630, Floor-mounted cabinet, IP55, Protection class 1, H:  
1950 mm, W: 800 mm, T: 250 mm, RAL 7035



Versão	
Nome da marca do produto	ALPHA 630
Designação do produto	Armário fixo
Processamento da superfície	Revestido a pó

  

Classe de protecção	
Classe de protecção IP	IP55
Aptidão para acção conjunta / Protecção contra raios	Sim
Aptidão para utilização / para uso exterior	Não

  

Aparência	
Código da cor RAL	RAL 7035
Componente do produto	
• Entrada de cabos	Sim
• Placa de montagem	Não
Expansão do produto / opcional / Encadeamento	Sim

  

Projeto mecânico	
Altura	1 950 mm
Largura	800 mm
Profundidade	250 mm

Profundidade da montagem	250 mm
Peso líquido	53 kg
material / da caixa	Aço

## Certificados

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

U  
UC

**General Product Approval**

**Declaration of  
Conformity**

**Test Certificates**



VDE



[Miscellaneous](#)



EG-Konf.

[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

**other**

[Miscellaneous](#)

## Outras informações

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=8GK1323-8KN33>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/pt/ps/8GK1323-8KN33>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KN33](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KN33)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



