

Class J fuse link 25 A 600 V quick-response, respect national installation rules!



Versão

Nome da marca do produto	SENTRON
Designação do produto	Encaixe de fusível cilíndrico
Execução do produto	estrutura cilíndrica

Dados técnicos gerais

Classe de operação do elemento fusível	rápido
Tamanho do elemento fusível	Classe J
Tipo de tensão	CA
Corrente / com AC / valor estipulado	25 A
Tensão de serviço / valor estipulado	600 V

Círculo principal

Corrente de funcionamento / valor nominal	25 A
---	------

Detalhes do produto

Componente do produto / Detector de choque	Não
Posição de montagem	opcional, preferível vertical
Peso líquido	46 g

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

General Product Approval



Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW4110-1HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW4110-1HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW4110-1HG

CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



