

SETRON, cylindrical fuse holder, 22x58 mm, 3-pole, In: 100 A, Un AC: 690 V



Versão	
Nome da marca do produto	SETRON
Designação do produto	Suporte de encaixe de fusível cilíndrico
Dados técnicos gerais	
Quantidade de pólos	3
Tamanho do cartucho de fusíveis	22x58 mm
Tensão de alimentação	
Corrente / com AC / valor estipulado	100 A
Tensão de serviço	
• com AC / valor estipulado	690 V
Classe de protecção IP	IP20
Projeto mecânico	
Altura	117 mm
Largura	108 mm
Profundidade	70 mm
Peso líquido	503 g
Certificados	

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F  
F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NW7231>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NW7231>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7231](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7231)

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





