

SITOR cylindrical fuse link, 22x127 mm, 40 A, gR, Un AC: 1500 V,
Un DC: 1000 V



Versão	
Nome da marca do produto	SETRON
Designação do produto	SITOR Elemento de fusível cilíndrico
Dados técnicos gerais	
Classe de operação do elemento fusível	gR
Tamanho do elemento fusível	22x127 mm
Tipo de tensão	CA
Corrente / com AC / valor estipulado	40 A
Tensão de alimentação / com DC	1 000 V
Tensão de serviço / valor estipulado	1 500 V
Circuito principal	
Corrente de funcionamento / valor nominal	40 A
Detalhes do produto	
Componente do produto / Detector de choque	Não
Posição de montagem	opcional, preferível vertical
Peso líquido	96 g
Certificados	

Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

General Product Approval

[Miscellaneous](#)

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NC2340-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NC2340-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2340-0MK

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



