

DIAZED fuse base Size DII Molded plastic, 3-pole touch-protected (BGV A2) Access: Double function terminal Outgoing feeder: Box terminal 25A 500 V AC



Versão	
Nome da marca do produto	SETRON
Designação do produto	Sistema de fusíveis DIAZED
Execução do produto	DIAZED-casquilho
Versão do casquilho para fusíveis	Fusível
Dados técnicos gerais	
Quantidade de pólos	3
Tamanho do sistema de fusíveis / segundo a DIN EN 60269-1	DII
Tensão de alimentação	
Corrente / com AC / valor estipulado	25 A
Tensão de alimentação / com AC / valor estipulado	500 V
Detalhes do produto	
Componente do produto / Cobertura	Sim
Projeto mecânico	
Altura	120 mm
Largura	80 mm
Profundidade	55 mm

Peso líquido	454 g
material / da caixa	plástico

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2 F
- segundo a IEC 81346-2:2009 F

Declaration of Conformity



EG-Konf.

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=5SF5068>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/5SF5068>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF5068

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



