

SR60 base DIAZED DIII 3-pole 690 V AC 500 V DC for Adapter screw for 5/10 mm busbar thickness with clamp-type terminals



Figure similar

Versão	
Nome da marca do produto	SETRON
Designação do produto	Sistema de fusíveis DIAZED
Execução do produto	CASQUILHO SR60
Versão do casquilho para fusíveis	Fusível
Dados técnicos gerais	
Quantidade de pólos	3
Tamanho do sistema de fusíveis / segundo a DIN EN 60269-1	DIII
Tensão de alimentação	
Corrente / com AC / valor estipulado	63 A
Tensão de alimentação / com AC / valor estipulado	690 V
Detalhes do produto	
Componente do produto / Cobertura	Não
Projeto mecânico	
Altura	200 mm

Largura	57 mm
Profundidade	43,5 mm
Peso líquido	290 g
material / da caixa	Outros

### Certificados

#### Indicadores de referência

- |  |   |
|--|---|
| <ul style="list-style-type: none"> <li>• segundo a DIN EN 61346-2</li> </ul>   | F |
| <ul style="list-style-type: none"> <li>• segundo a IEC 81346-2:2009</li> </ul> | F |

### Test Certificates

[Type Test Certificates/Test Report](#)

### Outras informações

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=5SF6215>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/5SF6215>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SF6215](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SF6215)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>

