

NEOZED, fuse base, D02, 3-pole, 63 A, Un AC: 400 V, Un DC: 250 V, for Busbar system 8US 60 mm



Versão	
Nome da marca do produto	NEOZED
Designação do produto	Base do fusível
Execução do produto	NEOZED casquilho montado em barramento
Variante de produto	para sistema de barramento 8US 60mm
Dados técnicos gerais	
Quantidade de pólos	3
Tamanho do sistema de fusíveis / segundo a DIN EN 60269-1	D02
Tensão de alimentação	
Tensão de serviço / valor estipulado	400 V
Dissipação	
Potência de perda [W] / com valor de corrente estipulado / com AC / com estado de funcionamento quente / por pólo	3 W
Circuito principal	
Corrente de funcionamento / valor estipulado	63 A

Detalhes do produto

Componente do produto / Cobertura Sim

Projeto mecânico

Altura	200 mm
Largura	36 mm
Profundidade	43 mm
Tipo de fixação	Sistema de barramento
Peso líquido	165 g
material / da base do fusível D	Plástico

Certificados

Indicadores de referência

- segundo a DIN EN 61346-2 F
- segundo a IEC 81346-2:2009 F

Declaration of Conformity



EG-Konf.

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=5SG6207>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/5SG6207>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG6207

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

