

shunt release 24-48 V DC, for miniature circuit breaker 5SL4, 5SY, 5SP, RCBO 5SU1, FI 5SV (for 5SU1 handle coupler 5ST3805-1 is required)



Versão	
Nome da marca do produto	SETRON
Designação do produto	Relé de abertura
Execução do produto	incorporável
vida útil eléctrica (ciclos de operação) / típico	20 000
Tensão de alimentação	
Tensão de serviço	
• valor estipulado	230 V
Classe de protecção IP	IP20
Detalhes do produto	
Expansão do produto	Relé de abertura
Número	
Número de comutadores de sinal de erro	0
Número de contactos de abertura	2
Número de contactos de fecho	0
Número de comutadores	0
Conexões	

Secção de condutor conectável	0,5 ... 2,5 mm ²
Binário de aperto / no caso de ligação com parafuso	0,5 N·m
Tipo de secções transversais dos condutores conectáveis / nos cabos AWG	24 ... 12

Projeto mecânico

Altura	90 mm
Largura	18 mm
Profundidade	70 mm
Peso líquido	90 g
<ul style="list-style-type: none"> • durante o funcionamento • durante o armazenamento 	-25 ... +55 °C -40 ... +75 °C

Certificados

Declaration of Conformity	other	Railway
---------------------------	-------	---------



EG-Konf.

[Environmental Confirmations](#)

[Miscellaneous](#)

[Vibration and Shock](#)

Outras informações

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=5ST3031>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/5ST3031>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5ST3031

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





