

SITOR cylindrical fuse link, 10 x 38 mm, 16 A, gR, Un AC: 690 V, Un DC: 440 V



Versão	
Nome da marca do produto	SETRON
Designação do produto	SITOR Elemento de fusível cilíndrico
Dados técnicos gerais	
Classe de operação do elemento fusível	gR
Tamanho do elemento fusível	10x38 mm
Tipo de tensão	CA
Corrente / com AC / valor estipulado	16 A
Tensão de alimentação / com DC	440 V
Tensão de serviço / valor estipulado	690 V
Circuito principal	
Corrente de funcionamento / valor nominal	16 A
Detalhes do produto	
Componente do produto / Detector de choque	Não
Posição de montagem	opcional, preferível vertical
Peso líquido	10 g
Certificados	

#### Indicadores de referência

- segundo a DIN EN 61346-2
- segundo a IEC 81346-2:2009

F

F

#### General Product Approval

[Miscellaneous](#)



UR

#### Outras informações

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/pt/pt/Catalog/product?mlfb=3NC1016-0MK>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/pt/ps/3NC1016-0MK>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NC1016-0MK](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1016-0MK)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



