

SR60 base DIAZED DII 3-pole 500 V AC DC for adaptor screw for 5/10 mm busbar thickness with clamp-type terminals



Рисунок аналогичен

версия	
Фирменное название продукта	SETRON
Наименование продукта	Система предохранителей DIAZED
Исполнение продукта	SR60-ЦОКОЛЬ
Исполнение цоколя предохранителя	Контрольная гильза
Общие технические данные	
Число полюсов	3
Типоразмер системы безопасности / согласно DIN EN 60269-1	DII
напряжение питания	
Ток / при переменном токе / расчетное значение	25 A
Напряжение питания / при переменном токе / расчетное значение	500 V
Подробнее	
Компонент продукта / крышка	нет
Механическая конструкция	

Высота	200 mm
Ширина	42 mm
Глубина	43,5 mm
вес-нетто	226 g
Материал / корпуса	прочее

#### Сертификаты

##### Условное обозначение

- согласно DIN EN 61346-2 F
- согласно IEC 81346-2:2009 F

#### Test Certificates

[Type Test Certificates/Test Report](#)

#### Дополнительная информация

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mfb=5SF6015>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/5SF6015>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=5SF6015](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5SF6015)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>

