

SENTRON, cylindrical fuse holder, 10x38 mm, 2-pole, In: 32 A, Un AC: 690 V, LED signal detector



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Держатель цилиндрических предохранителей
Исполнение продукта	Светодиодный сигнализатор
Общие технические данные	
Число полюсов	2
Типоразмер плавких вставок предохранителей	10 x 38 мм
напряжение питания	
Ток / при переменном токе / расчетное значение	32 A
рабочее напряжение	
• при переменном токе / расчетное значение	690 V
Степень защиты IP	IP20
Механическая конструкция	
Высота	81 mm
Ширина	36 mm
Глубина	64 mm
вес-нетто	136 g

## Сертификаты

### Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

### General Product Approval

### Declaration of Conformity



UR



EG-Konf.

## Дополнительная информация

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NW7024>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW7024>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW7024](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7024)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>





