

SENTRON, cylindrical fuse holder, 10x38 mm, 1P+N, In: 32 A, Un AC: 690 V, LED signal detector



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Держатель цилиндрических предохранителей
Исполнение продукта	Светодиодный сигнализатор
Общие технические данные	
Число полюсов	2
Число полюсов / примечание	1P+N
Типоразмер плавких вставок предохранителей	10 x 38 мм
напряжение питания	
Ток / при переменном токе / расчетное значение	32 A
рабочее напряжение	
• при переменном токе / расчетное значение	690 V
Степень защиты IP	IP20
Механическая конструкция	
Высота	81 mm
Ширина	18 mm
Глубина	64 mm
вес-нетто	75 g

Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F
F

General Product Approval

Declaration of Conformity



UR



EG-Konf.

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mfb=3NW7054>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW7054>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7054

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





