

SENTRON, cylindrical fuse holder, 22x58 mm, 3P+N, In: 100 A, Un AC: 690 V, LED signal detector



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Держатель цилиндрических предохранителей
Исполнение продукта	Светодиодный сигнализатор
Общие технические данные	
Число полюсов	4
Число полюсов / примечание	3P+N
Типоразмер плавких вставок предохранителей	22x58 мм
напряжение питания	
Ток / при переменном токе / расчетное значение	100 A
рабочее напряжение	
• при переменном токе / расчетное значение	690 V
Степень защиты IP	IP20
Механическая конструкция	
Высота	117 mm
Ширина	144 mm
Глубина	70 mm
вес-нетто	686 g

## Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F  
F

## Declaration of Conformity



EG-Konf.

## Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mfb=3NW7262>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW7262>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=3NW7262](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=3NW7262)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>





