

ALPHA 400, wall-mounted cabinet, IP55, Protection class 2, H: 1100 mm, W: 1050 mm, T: 210 mm, RAL 9016



версия	
Фирменное название продукта	ALPHA 400
Наименование продукта	Стенной шкаф
Исполнение продукта	Открытая прокладка
Обработка поверхности	порошковая окраска
класс защиты	
Степень защиты IP	IP55
Пригодность к взаимодействию / молниезащита	да
Пригодность к использованию / для внешнего использования	нет
появление	
Номер цвета RAL	RAL 9016
Компонент продукта	
• Кабельный ввод	да
• монтажная плита	нет
Расширение продукта / дополнительно / последовательное соединение	да
Механическая конструкция	

Высота	1 100 mm
Ширина	1 050 mm
Глубина	210 mm
Монтажная глубина	210 mm
вес-нетто	33 kg
Материал / корпуса	сталь

### Сертификаты

Условное обозначение	
<ul style="list-style-type: none"> <li>согласно DIN EN 61346-2</li> <li>согласно IEC 81346-2:2009</li> </ul>	U UC

General Product Approval	Declaration of Conformity	Test Certificates	other
--------------------------	---------------------------	-------------------	-------



[Miscellaneous](#)



[Special Test Certificate](#)

[Miscellaneous](#)

### Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=8GK1133-5KA42>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/8GK1133-5KA42>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1133-5KA42](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1133-5KA42)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



