

ALPHA 630, Floor-mounted cabinet, IP43, Protection class 1, H: 1950 mm, W: 800 mm, T: 210 mm, RAL 7035, incl. flange in roof



версия	
Фирменное название продукта	ALPHA 630
Наименование продукта	Напольный шкаф
Обработка поверхности	порошковая окраска
класс защиты	
Степень защиты IP	IP43
Пригодность к взаимодействию / молниезащита	да
Пригодность к использованию / для внешнего использования	нет
появление	
Номер цвета RAL	RAL 7035
Компонент продукта	
• Кабельный ввод	да
• монтажная плита	нет
Специальная характеристика продукта	Включая фланец в крыше
Расширение продукта / дополнительно / последовательное соединение	да
Механическая конструкция	

Высота	1 950 mm
Ширина	800 mm
Глубина	210 mm
Монтажная глубина	210 mm
вес-нетто	49 kg
Материал / корпуса	сталь

Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

U

UC

General Product Approval

Test Certificates

other



[Special Test Certificate](#)

[Miscellaneous](#)

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=8GK1322-8KA32>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/8GK1322-8KA32>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1322-8KA32

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



