

ALPHA 630, Floor-mounted cabinet, IP55, Protection class 1, H: 1950 mm, W: 300 mm, T: 320 mm, RAL 7035



версия	
Фирменное название продукта	ALPHA 630
Наименование продукта	Напольный шкаф
Обработка поверхности	порошковая окраска
класс защиты	
Степень защиты IP	IP55
Пригодность к взаимодействию / молниезащита	да
Пригодность к использованию / для внешнего использования	нет
появление	
Номер цвета RAL	RAL 7035
Компонент продукта	
• Кабельный ввод	да
• монтажная плата	нет
Расширение продукта / дополнительно / последовательное соединение	да
Механическая конструкция	
Высота	1 950 mm

Ширина	300 mm
Глубина	320 mm
Монтажная глубина	320 mm
вес-нетто	32,5 kg
Материал / корпуса	сталь

## Сертификаты

### Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



VDE

[Miscellaneous](#)



EG-Konf.

[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

## other

[Miscellaneous](#)

## Дополнительная информация

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=8GK1323-8KN14>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/8GK1323-8KN14>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KN14](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KN14)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://www.siemens.com/specifications>



