

ALPHA 630, Floor-mounted cabinet, with open side wall, IP55,  
Protection class 1, H: 1950 mm, W: 800 mm, T: 250 mm, RAL 7035



версия	
Фирменное название продукта	ALPHA 630
Наименование продукта	Напольный шкаф
Исполнение продукта	С открытой боковой стенкой
Обработка поверхности	порошковая окраска
класс защиты	
Степень защиты IP	IP55
Пригодность к взаимодействию / молниезащита	да
Пригодность к использованию / для внешнего использования	нет
появление	
Номер цвета RAL	RAL 7035
Компонент продукта	
• Кабельный ввод	да
• монтажная плита	нет
Расширение продукта / дополнительно / последовательное соединение	да
Механическая конструкция	

Высота	1 950 mm
Ширина	800 mm
Глубина	250 mm
Монтажная глубина	250 mm
вес-нетто	46,5 kg
Материал / корпуса	сталь

## Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Miscellaneous](#)



[Type Test Certificates/Test Report](#)

[Special Test Certificate](#)

### other

[Miscellaneous](#)

## Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=8GK1323-8KP33>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/8GK1323-8KP33>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1323-8KP33](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1323-8KP33)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



