

Accessory for 3KD size 2 door-coupling rotary operating mechanism
Complete operating mechanism, gray incl. shaft 300 mm long and
clutch holder Can be locked in OFF position



версия	
Фирменное название продукта	SETRON
Наименование продукта	Принадлежности для выключателя нагрузки-разъединителя
Исполнение продукта	Поворотный привод с выводом на дверь
Исполнение коммутационного привода	РУЧНОЙ ПРИВОД
Степень защиты IP / с лицевой стороны	IP65
пригодность	
Пригодность к использованию	Для 3KD, типоразмер 2
появление	
Цвет / элемента управления	серый
Подробнее	
Описание продукта	ВКЛЮЧАЯ ХВОСТОВИК И ШТИФТ НАЖИМНОГО ДИСКА СЦЕПЛЕНИЯ
Характеристики продукта	
<ul style="list-style-type: none"> • блокировка в положении ВЫКЛ. 	да
<ul style="list-style-type: none"> • Блокировка 	да
Исполнение индикации / максимальный	ВКЛ.-ВЫКЛ.

Механическая конструкция

Высота	75 mm
Ширина	99,5 mm
Глубина	366 mm
Длина / удлинительного вала	300 mm
вес-нетто	347 g

Сертификаты

General Product Approval	Declaration of Conformity	Shipping Approval	other
--------------------------	---------------------------	-------------------	-------

[Miscellaneous](#)



EG-Konf.



LRS

[Miscellaneous](#)

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3KD9215-1>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3KD9215-1>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3KD9215-1

CAx-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



