

SITOR cylindrical fuse link, 22x127 mm, 20 A, gS, Un AC: 1500 V,
Un DC: 1000 V



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Плавкая вставка цилиндрического предохранителя SITOR
Общие технические данные	
Эксплуатационный класс вставки предохранителя	gS
Размер вставки предохранителя	22x127 мм
Вид напряжения	перем. ток
Ток / при переменном токе / расчетное значение	20 A
Напряжение питания / при постоянном токе	1 000 V
рабочее напряжение / расчетное значение	1 500 V
Главная цепь	
Рабочий ток / номинальное значение	20 A
Подробнее	
Компонент продукта / сигнализатор удара	нет
Монтажное положение	Произвольно, предпочтительно вертикально
вес-нетто	96 g
Сертификаты	

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

General Product Approval

[Miscellaneous](#)

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NC2320-0MK>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NC2320-0MK>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC2320-0MK

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



