

SENTRON, cylindrical fuse link, Class CC, 25 A, time-lag, current-limiting, Un AC: 600 V, respect national installation rules!



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Цилиндрическая предохранительная вставка
Общие технические данные	
Эксплуатационный класс вставки предохранителя	Инерционный, с ограничением тока
Размер вставки предохранителя	Класс срабатывания CC
Вид напряжения	перем. ток
Ток / при переменном токе / расчетное значение	25 A
рабочее напряжение / расчетное значение	600 V
Главная цепь	
Рабочий ток / номинальное значение	25 A
Подробнее	
Компонент продукта / сигнализатор удара	нет
Монтажное положение	Произвольно, предпочтительно вертикально
вес-нетто	6 g
Сертификаты	
Условное обозначение	

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

### General Product Approval

### Declaration of Conformity



### Дополнительная информация

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

#### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NW3250-0HG>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW3250-0HG>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=3NW3250-0HG](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW3250-0HG)

#### CAX-Online-Generator

<http://www.siemens.com/cax>

#### Tender specifications

<http://www.siemens.com/specifications>

