

SENTRON, cylindrical fuse link, Class CC, 30 A, time-lag, current-limiting, Un AC: 600 V, respect national installation rules!



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Цилиндрическая предохранительная вставка
Общие технические данные	
Эксплуатационный класс вставки предохранителя	Инерционный, с ограничением тока
Размер вставки предохранителя	Класс срабатывания CC
Вид напряжения	перем. ток
Ток / при переменном токе / расчетное значение	30 A
рабочее напряжение / расчетное значение	600 V
Главная цепь	
Рабочий ток / номинальное значение	30 A
Подробнее	
Компонент продукта / сигнализатор удара	нет
Монтажное положение	Произвольно, предпочтительно вертикально
вес-нетто	7 g
Сертификаты	
Условное обозначение	

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F
F

General Product Approval

Declaration of Conformity



CSA

UL

EG-Konf.

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NW3300-0HG>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW3300-0HG>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW3300-0HG

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

