

SETRON, cylindrical fuse holder, 10x38 mm, 3-pole, In: 30 A, Un
AC: 600 V, Flat version



версия	
Фирменное название продукта	SETRON
Наименование продукта	Держатель цилиндрических предохранителей
Исполнение продукта	Плоское исполнение
Общие технические данные	
Число полюсов	3
Типоразмер плавких вставок предохранителей	10 x 38 мм
напряжение питания	
Ток / при переменном токе / расчетное значение	30 A
рабочее напряжение	600 V
• при переменном токе / расчетное значение	
Степень защиты IP	IP20
Механическая конструкция	
Высота	76 mm
Ширина	60,5 mm
Глубина	26 mm
вес-нетто	103 g

Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

General Product Approval



CSA



UR

[Miscellaneous](#)

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NC1038-3>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NC1038-3>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NC1038-3

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



