

SENTRON, cylindrical fuse holder, 10 x 38 mm, 2-pole, In: 25 A, Ue DC: 1000 V, LED Signal detector, for photovoltaic application



версия

Фирменное название продукта	SENTRON
Наименование продукта	Держатель цилиндрических предохранителей
Исполнение продукта	Светодиодный сигнализатор, для фотоэлектрического оборудования

Общие технические данные

Число полюсов	2
Типоразмер плавких вставок предохранителей	10 x 38 мм

напряжение питания

Ток / при переменном токе / расчетное значение	25 A
рабочее напряжение	
• при постоянном токе / расчетное значение	1 000 V
Степень защиты IP	IP20

Механическая конструкция

Высота	85 mm
Ширина	36 mm
Глубина	65 mm
вес-нетто	123 g

Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

General Product Approval

Declaration of Con-
formity

other



CSA



UL



EG-Konf.

[Miscellaneous](#)

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NW7024-4>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW7024-4>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7024-4

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

