

SENTRON, cylindrical fuse holder, 22x58 mm, 3-pole, In: 100 A, Un AC: 690 V



версия	
Фирменное название продукта	SENTRON
Наименование продукта	Держатель цилиндрических предохранителей
Общие технические данные	
Число полюсов	3
Типоразмер плавких вставок предохранителей	22x58 мм
напряжение питания	
Ток / при переменном токе / расчетное значение	100 A
рабочее напряжение	
• при переменном токе / расчетное значение	690 V
Степень защиты IP	IP20
Механическая конструкция	
Высота	117 mm
Ширина	108 mm
Глубина	70 mm
вес-нетто	503 g
Сертификаты	

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

Declaration of Conformity

Test Certificates



EG-Konf.

[Miscellaneous](#)

Дополнительная информация

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=3NW7231>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/ru/ps/3NW7231>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3NW7231

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>





