

ALPHA 630, Floor-mounted cabinet, Flat Pack, IP43, Protection class 1, H: 1900 mm, W: 300 mm, T: 210 mm, RAL 7035



версия	
Фирменное название продукта	ALPHA 630
Наименование продукта	Напольный шкаф
Исполнение продукта	Плоский корпус
Обработка поверхности	порошковая окраска
класс защиты	
Степень защиты IP	IP43
Пригодность к взаимодействию / молниезащита	да
Пригодность к использованию / для внешнего использования	нет
появление	
Номер цвета RAL	RAL 7035
Компонент продукта	
• Кабельный ввод	да
• монтажная плата	нет
Расширение продукта / дополнительно / последовательное соединение	да
Механическая конструкция	

Высота	1 900 mm
Ширина	300 mm
Глубина	210 mm
Монтажная глубина	210 mm
вес-нетто	26,5 kg
Материал / корпуса	сталь

## Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

U

UC

### General Product Approval

### Declaration of Conformity

### Test Certificates



[Miscellaneous](#)



[Special Test Certificate](#)

[Type Test Certificates/Test Report](#)

### other

[Miscellaneous](#)

## Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=8GK1302-8KK12>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/8GK1302-8KK12>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1302-8KK12](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1302-8KK12)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



