

NEOZED, fuse base, D03, 1-pole, 100 A, Un AC: 400 V, Un DC: 250 V, without cover



Рисунок аналогичен

версия	
Фирменное название продукта	NEOZED
Наименование продукта	Основание плавкой вставки
Вариант продукта	Без крышки
Общие технические данные	
Число полюсов	1
Типоразмер системы безопасности / согласно DIN EN 60269-1	D03
напряжение питания	
рабочее напряжение / расчетное значение	400 V
рассеивание	
Мощность потерь [Вт] / при расчётном токе / при переменном токе / при теплом эксплуатационном состоянии / на полюс	2,5 W
Главная цепь	
Рабочий ток / расчетное значение	100 A

## Подробнее

Компонент продукта / крышка	нет
-----------------------------	-----

## Механическая конструкция

Высота	86 mm
Ширина	44,9 mm
Глубина	44 mm
Вид крепления	DIN-рейка
вес-нетто	204 g
Материал / цоколя предохранителей D	Фарфор

## Сертификаты

Условное обозначение	
• согласно DIN EN 61346-2	F
• согласно IEC 81346-2:2009	F

Declaration of Con-  
formity

Test Certificates



EG-Konf.

[Special Test Certificate](#)

[Type Test  
Certificates/Test Report](#)

[Miscellaneous](#)

## Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=5SG1812>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/5SG1812>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG1812](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG1812)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>

