

NEOZED, fuse base, D02, 3-pole, 63 A, Un AC: 400 V, Un DC: 250 V



## версия

Фирменное название продукта	NEOZED
Наименование продукта	Основание плавкой вставки

## Общие технические данные

Число полюсов	3
Типоразмер системы безопасности / согласно DIN EN 60269-1	D02

## напряжение питания

рабочее напряжение / расчетное значение	400 V
---	-------

## рассеивание

Мощность потерь [Вт] / при расчётном токе / при переменном токе / при теплом эксплуатационном состоянии / на полюс	3 W
--	-----

## Главная цепь

Рабочий ток / расчетное значение	63 A
----------------------------------	------

## Подробнее

Компонент продукта / крышка	да
-----------------------------	----

## Механическая конструкция

Высота	83 mm
Ширина	81 mm
Глубина	64 mm
Вид крепления	DIN-рейка
вес-нетто	389 g
Материал / цоколя предохранителей D	Пластмасса

## Сертификаты

Условное обозначение

- согласно DIN EN 61346-2
- согласно IEC 81346-2:2009

F

F

General Product Approval	Declaration of Conformity	Test Certificates
--------------------------	---------------------------	-------------------



VDE



EG-Konf.

[Type Test Certificates/Test Report](#)

## Дополнительная информация

**Information- and Downloadcenter (Catalogs, Brochures,...)**

<http://www.siemens.com/lowvoltage/catalogs>

**Industry Mall (Online ordering system)**

<https://mall.industry.siemens.com/mall/ru/ru/Catalog/product?mlfb=5SG5701>

**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**

<https://support.industry.siemens.com/cs/ww/ru/ps/5SG5701>

**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=5SG5701](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=5SG5701)

**CAX-Online-Generator**

<http://www.siemens.com/cax>

**Tender specifications**

<http://www.siemens.com/specifications>



