

**Skruvmejsel
SDIS 1.0X5.5X125**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



VDE-isolerad spårskruvmejsel, SDI DIN 7437, ISO 2380/2, klingprofil enligt DIN 5264, ISO 2380/1, SoftFinish-handtag

Allmänna beställningsdata

| | |
|-------------------|--|
| Typ | SDIS 1.0X5.5X125 |
| Art.nr. | 9008410000 |
| Artikelbeteckning | Skruvmejsel, Klingbredd (B): 5.5 mm, Klinglängd: 125 mm, Klingtjocklek: 1 mm |
| GTIN (EAN) | 4032248056378 |
| Frp | 1 Stück |

**Skruvmejsel
SDIS 1.0X5.5X125**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data**Mått och vikter**

| | | | |
|----------|--------|-----------------|------------|
| Bredd | 245 mm | Byggbredd (tum) | 9,646 inch |
| vikt | 98 g | Nettovikt | 92,6 g |
| Diameter | 36 mm | | |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

| | | | |
|----------------|--------|------------|--------|
| Bladtyp | B | Form | Spår |
| Klingbredd (B) | 5,5 mm | Klinglängd | 125 mm |
| Klingtjocklek | 1 mm | | |

Klassificeringar

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001395 | ETIM 4.0 | EC000174 |
| ETIM 5.0 | EC000174 | ETIM 6.0 | EC000158 |
| UNSPSC | 27-11-17-01 | eClass 5.1 | 21-04-04-01 |
| eClass 6.2 | 21-04-04-01 | eClass 7.1 | 21-04-04-90 |
| eClass 8.1 | 21-04-04-90 | eClass 9.0 | 21-04-04-07 |
| eClass 9.1 | 21-04-04-07 | | |

Godkännanden

Godkännanden

**Downloads**

| | |
|---|---|
| Broschyr/Katalog | CAT 4.3 ELECTR 15/16 EN CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN CAT 2 PORTFOLIOGUIDE EN |
| Godkännande/Certifikat/Dokument om överensstämmelse | Manufacturer's Declaration - Screwdrivers Declaration of the Manufacturer |