

**Skruvmejsel
SDIS 1.2X6.5X150**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

Produktillustration



Avbildning liknande

VDE-isolerad spårskruvmejsel, SDI DIN 7437, ISO 2380/2, klingprofil enligt DIN 5264, ISO 2380/1, SoftFinish-handtag

Allmänna beställningsdata

Typ	SDIS 1.2X6.5X150
Art.nr.	9008420000
Artikelbeteckning	Skruvmejsel, Klingbredd (B): 6.5 mm, Klinglängd: 150 mm, Klingtjocklek: 1.2 mm
GTIN (EAN)	4032248056385
Frp	1 Stük

**Skruvmejsel
SDIS 1.2X6.5X150**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data**Mått och vikter**

Bredd	270 mm	Byggbredd (tum)	10,63 inch
vikt	112 g	Nettovikt	104,1 g
Diameter	36 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

Bladtyp	B	Form	Spår
Klingbredd (B)	6,5 mm	Klinglängd	150 mm
Klingtjocklek	1,2 mm		

Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000158
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-07
eClass 9.1	21-04-04-07		

Godkännanden

Godkännanden

**Downloads**

Broschyr/Katalog	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN CAT 2 PORTFOLIOGUIDE EN
Godkännande/Certifikat/Dokument om överensstämmelse	Manufacturer's Declaration - Screwdrivers Declaration of the Manufacturer