

**Skruvmejsel
SDIZ 0.6X3.5X100**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



VDE-isolerad spårskruvmejsel, SDI DIN 7437, ISO 2380/2, klingprofil enligt DIN 5264, ISO 2380/1, SoftFinish-handtag

Allmänna beställningsdata

Typ	SDIZ 0.6X3.5X100
Art.nr.	9008450000
Artikelbeteckning	Skruvmejsel, Klingbredd (B): 3.5 mm, Klinglängd: 100 mm, Klingtjocklek: 0.6 mm
GTIN (EAN)	4032248056446
Frp	1 Stück

Datablad

Skruvmejsel SDIZ 0.6X3.5X100

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data

Mått och vikter

Bredd	205 mm	Byggbredd (tum)	8,071 inch
vikt	44,4 g	Nettovikt	35,9 g

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

Form	Spår med tapp	Klingbredd (B)	3,5 mm
Klinglängd	100 mm	Klingtjocklek	0,6 mm

Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000149
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-50-03
eClass 9.1	21-04-04-90		

Godkännanden

Godkännanden



Downloads

Broschyr/Katalog [CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)

Godkännande/Certifikat/Dokument om överensstämmelse [Manufacturer's Declaration - Screwdrivers](#)