

**Skruvmejsel
SDIK PH2**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



VDE-isolerad kryssmejsel, Typ Phillips, SDIK PH DIN
7438, ISO 8764/2-PH, klingprofil enligt ISO 8764-PH,
SoftFinish-handtag

Allmänna beställningsdata

Typ	SDIK PH2
Art.nr.	9008580000
Artikelbeteckning	Skruvmejsel, Klinglängd: 100 mm
GTIN (EAN)	4032248056576
Frp	1 Stük

**Skruvmejsel
SDIK PH2**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data**Mått och vikter**

Bredd	220 mm	Byggbredd (tum)	8,661 inch
vikt	104 g	Nettovikt	97 g
Diameter	36 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

Form	Philips	Klinglängd	100 mm
storlek	2		

Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000144
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-06
eClass 9.1	21-04-04-06		

Godkännanden

Godkännanden

**Downloads**

Broschyr/Katalog [CAT 4.3 ELECTR 15/16 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)

Godkännande/Certifikat/Dokument om överensstämmelse [Manufacturer's Declaration - Screwdrivers](#)