

**Skruvmejsel
SDIK PH3****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

1000 V
IEC 60900

VDE-isolerad kryssmejsel, Typ Phillips, SDIK PH DIN
7438, ISO 8764/2-PH, klingprofil enligt ISO 8764-PH,
SoftFinish-handtag

Allmänna beställningsdata

Typ	SDIK PH3
Art.nr.	9008590000
Artikelbeteckning	Skruvmejsel, Klinglängd: 150 mm
GTIN (EAN)	4032248056590
Frp	1 Stük

Datablad

Skruvmejsel SDIK PH3

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data

Mått och vikter

Bredd	270 mm	Byggbredd (tum)	10,63 inch
vikt	171 g	Nettovikt	160,1 g
Diameter	41 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

Form	Philips	Klinglängd	150 mm
storlek	3		

Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000144
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-06
eClass 9.1	21-04-04-06		

Godkännanden

Godkännanden



Downloads

Broschyr/Katalog	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN
Godkännande/Certifikat/Dokument om överensstämmelse	Manufacturer's Declaration - Screwdrivers