

**Skruvmejsel
SDIK PZ1**

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com



VDE-isolerad kryssmejsel, Typ Pozidriv, SDIK PZ DIN 7438, ISO 8764/2-PZ, klingprofil enligt ISO 8764-PZ, SoftFinish-handtag

Allmänna beställningsdata

Typ	SDIK PZ1
Art.nr.	9008900000
Artikelbeteckning	Skruvmejsel, Klinglängd: 80 mm
GTIN (EAN)	4032248266685
Frp	1 Stük

**Skruvmejsel
SDIK PZ1**

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Tekniska data**Mått och vikter**

Bredd	191 mm	Byggbredd (tum)	7,52 inch
vikt	54 g	Nettovikt	64 g
Diameter	30 mm		

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

Form	Pozidrive	Klinglängd	80 mm
storlek	1		

Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC000174
ETIM 5.0	EC000174	ETIM 6.0	EC000144
UNSPSC	27-11-17-01	eClass 5.1	21-04-04-01
eClass 6.2	21-04-04-01	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.0	21-04-04-06
eClass 9.1	21-04-04-06		

Godkännanden

Godkännanden

**Downloads**

Broschyr/Katalog	CAT 6 TOOLS 15/16 EN CAT 5 ENCL 17/18 EN
Godkännande/Certifikat/Dokument om överensstämmelse	Manufacturer's Declaration - Screwdrivers