

WK S 0,8X4,0**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Utbytesklingor till vridmomentsskruvmejsel**

Klingprofil enligt DIN 5264, ISO 2380/1

Allmänna beställningsdata

| | |
|-------------------|--|
| Typ | WK S 0,8X4,0 |
| Art.nr. | 9918550000 |
| Artikelbeteckning | Skruvmejselinsats, Klingbredd (B): 4 mm, 175 mm, Klingtjocklek: 0.8 mm |
| GTIN (EAN) | 4032248388912 |
| Frp | 1 Stück |

WK S 0,8X4,0

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Tekniska data

Mått och vikter

| | | | |
|-------|--------|-----------------|------------|
| Bredd | 175 mm | Byggbredd (tum) | 6,89 inch |
| Höjd | 4 mm | Bygghöjd (tum) | 0,157 inch |
| Djup | 4 mm | Byggdjup (tum) | 0,157 inch |
| vikt | 22 g | Nettovikt | 25 g |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skruvverktyg

| | | | |
|------------|--------|----------------|--------|
| Form | Spår | Klingbredd (B) | 4 mm |
| Klinglängd | 175 mm | Klingtjocklek | 0,8 mm |

Klassificeringar

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001395 | ETIM 4.0 | EC001395 |
| ETIM 5.0 | EC001395 | ETIM 6.0 | EC002116 |
| UNSPSC | 27-11-28-14 | eClass 5.1 | 21-04-04-02 |
| eClass 6.2 | 21-04-92-21 | eClass 7.1 | 21-04-04-90 |
| eClass 8.1 | 21-04-04-90 | eClass 9.1 | 21-04-04-90 |

Godkännanden

Godkännanden



Downloads

Broschyr/Katalog [CAT 3 HDC 17/18 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)