

**WK S 1,0x5,5****Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

**Utbytesklingor till vridmomentsskruvmejsel**

Klingprofil enligt DIN 5264, ISO 2380/1

**Allmänna beställningsdata**

Typ	WK S 1,0x5,5
Art.nr.	<a href="#">9918560000</a>
Artikelbeteckning	Skruvmejselinsats, Klingbredd (B): 5.5 mm, 175 mm, Klingtjocklek: 1 mm
GTIN (EAN)	4032248388936
Frp	1 Stück

## WK S 1,0x5,5

Weidmüller Interface GmbH &amp; Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

## Tekniska data

## Mått och vikter

Bredd	175 mm	Byggbredd (tum)	6,89 inch
Höjd	4 mm	Bygghöjd (tum)	0,157 inch
Djup	4 mm	Byggdjup (tum)	0,157 inch
vikt	22 g	Nettovikt	24 g

## Environmental Product Compliance

REACH SVHC Lead 7439-92-1

## Skruvverktyg

Form	Spår	Klingbredd (B)	5,5 mm
Klinglängd	175 mm	Klingtjocklek	1 mm

## Klassificeringar

ETIM 3.0	EC001395	ETIM 4.0	EC001395
ETIM 5.0	EC001395	ETIM 6.0	EC002116
UNSPSC	27-11-28-14	eClass 5.1	21-04-04-02
eClass 6.2	21-04-92-21	eClass 7.1	21-04-04-90
eClass 8.1	21-04-04-90	eClass 9.1	21-04-04-90

## Godkännanden

Godkännanden



## Downloads

Broschyr/Katalog [CAT 3 HDC 17/18 EN](#)  
[CAT 6 TOOLS 15/16 EN](#)  
[CAT 5 ENCL 17/18 EN](#)