

WK K PH1**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com**Utbytesklingor till vridmomentsskruvmejsel**

Klingprofil enligt DIN 5260-PH, ISO 8764/1-PH

Allmänna beställningsdata

| | |
|-------------------|------------------------------|
| Typ | WK K PH1 |
| Art.nr. | 9918580000 |
| Artikelbeteckning | Skruvmejselinsats, 175 mm, 1 |
| GTIN (EAN) | 4032248388950 |
| Frp | 1 Stück |

WK K PH1

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Tekniska data

Mått och vikter

| | | | |
|-------|--------|-----------------|------------|
| Bredd | 175 mm | Byggbredd (tum) | 6,89 inch |
| Höjd | 4 mm | Bygghöjd (tum) | 0,157 inch |
| Djup | 4 mm | Byggdjup (tum) | 0,157 inch |
| vikt | 25 g | Nettovikt | 25 g |

Environmental Product Compliance

REACH SVHC Lead 7439-92-1

Skrivverktyg

| | | | |
|--------------------|-----------|------------|--------|
| Form | Crosshead | Klinglängd | 175 mm |
| Klingmått krysspår | 1 | storlek | 1 |

Klassificeringar

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001395 | ETIM 4.0 | EC001395 |
| ETIM 5.0 | EC001395 | ETIM 6.0 | EC002115 |
| UNSPSC | 27-11-28-14 | eClass 5.1 | 21-04-04-02 |
| eClass 6.2 | 21-04-92-21 | eClass 7.1 | 21-04-04-90 |
| eClass 8.1 | 21-04-04-90 | eClass 9.1 | 21-04-04-90 |

Godkännanden

Godkännanden



Downloads

Broschyr/Katalog [CAT 3 HDC 17/18 EN](#)
[CAT 6 TOOLS 15/16 EN](#)
[CAT 5 ENCL 17/18 EN](#)